



100ml aerosol bottle with belt clip



EYEAID

“Time is the single most important factor when it comes to saving your eyesight.”



Ideal for use after using a plumbed-in eye wash when transporting a patient to hospital. Also for use by those working on sites that requires a portable solution.

eyeaid is also available in a 100ml aerosol bottle and can be supplied with a belt clip.

Content in each 250ml can

Ingredient	CAS no	Weight in %
Sodium Dihydrogenphosfat	13472-35-0	<1
Sodium Chloride, USP	7647-14-5	0,9
Sodium Hydroxid	1310-73-2	Adjusted to pH7,4
Aqua, USP		100
Nitrogen, USP	7727-37-9	

Technical Specification - Spray Can

250ml 0,9% buffered sodium chloride
Nitrogen based aerosol can
Pressure - 4 Bar
Plastic material: Borealis BC245MO (PP)
Net weight 315g
Shelf life 2+ years

eyeaid

- In line with the minimum rinsing time requirements of ANSI ensuring more than 15 minutes rinsing time per 250ml aerosol spray can
- EU-Certified
- Single hand operated and easy to use
- Rinses the eye fast and effectively
- Ensures an optimal view to the eye during rinsing
- Cost effective

Hughes Safety Showers are proud to introduce **eyeaid** to the market. **eyeaid** is a single hand operated portable eye wash that is quick, easy and effective to use. It only takes one movement to start rinsing the eye.

eyeaid has a unique eye opening feature that simplifies the flushing process and eliminates the risk of further contamination from contaminated fingers.

Each aerosol spray can contains 250ml of sterile saline eye wash solution, giving a minimum of 15 minutes rinsing for removing dangerous chemicals or foreign bodies from the eye.

On the **eyeaid** eye opener there is a seal that shows whether the bottle has been used. **If the seal is broken replace the bottle immediately.**



HUGHES



HUGHES-SAFETY-SHOWERS.CO.UK



THE QUEEN'S AWARDS
FOR ENTERPRISE
INTERNATIONAL TRADE
2012



Health & Wellbeing
Award



Champion





Polystyrene insulated box



Wall Station

Take good care of your eyes, they cannot be replaced.

eyeaid Wall Station

Hughes Safety Showers also supply an **eyeaid** Wall Station that includes two 250ml bottles. The station ensures quick access to the aerosol spray cans and protects them from dirt and dust.


eyeaid offers great value for money through an innovative delivery method and long rinsing time at a lower cost.

It is recommended that the **eyeaid** eye wash station is mounted in an appropriate place where it is highly visible and easily accessible. The Wall Station should be mounted so that the top edge of the station is 165-170cm above the level of the floor. The station is mounted on the wall using the four screw holes on the rear of the metal bracket.

A portable Polystyrene insulated box with a 12 volt heating element (including a 250ml **eyeaid**) is available on request. Ideal for those working in colder climates.

eyeaid products available from Hughes Safety Showers include:

- Wall Station including two 250ml aerosol bottles
- Polystyrene box with a 12 volt heating element including 250ml aerosol bottle
- 100ml bottle with belt clip
- 250ml and 100ml refill bottles



Technical Specification - EYE Aid Station

Holder	2mm steel with powder coating
Front Lid	2mm acrylic (axpet) with silk print
Dimensions	320 x 175 x 103mm



HUGHES SAFETY SHOWERS LTD
Whitefield Road, Bredbury, Stockport, Cheshire, SK6 2SS England, UK.

T: +44 (0)161 430 6618

E: info@hughes-safety-showers.co.uk F: +44 (0)161 430 7928

www.hughes-safety-showers.co.uk

Registered No. 0939240. VAT Registration No. 918 5005 32. Hughes Safety Showers Ltd is a wholly owned subsidiary of the JD Hughes Group PLC.

